

# 022200-00 Cut Sheet



Stego Varioline LED enclosure light, 100-240 VAC operating voltage, no switch, 23.4in length, 1730 Lm, screw mount, 2-pole plug with snap lock, 16W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/022200-00>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	LED enclosure light
<b>Series</b>	Varioline
<b>Operating Voltage</b>	100-240 VAC
<b>Switch Type</b>	None
<b>Length</b>	23.4in
<b>Luminous Flux</b>	1730 Lm
<b>Integral Receptacle</b>	No
<b>Mounting</b>	Screw
<b>Connection</b>	2-pole plug with snap lock
<b>Power Consumption</b>	16W
<b>IP Rating</b>	IP20
<b>Requires</b>	Power or extension cable

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/022200-00.pdf>  
See store item page for other formats.