02534.1-00 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Stego LED enclosure light, 120 VAC operating voltage, on/off/motion sensor switch, 13.6in length, 560 lm, integral receptacle, screw or magnet mount, 2-pole pressure clamp for 14 AWG stranded or solid wire, 4W, IP20.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/02534.1-00

Technical Specifications

Brand	Stego
Item	LED enclosure light
Operating Voltage	120 VAC
Switch Type	On/off/motion sensor
Length	13.6in
Luminous Flux	560 lm
Color Temperature	6000–7000K

Integral Receptacle	Yes
Mounting	Screw or magnet
Connection	2-pole pressure clamp for 14 AWG stranded or solid wire
Power Consumption	4W
IP Rating	IP20
Rotatable	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/02534.1-00.pdf
See store item page for other formats.