

# 025401-10 Cut Sheet



Stego Ecoline LED enclosure light, 24-48 VDC operating voltage, on/off switch, 13.8in length, 400 Lm, magnet mount, 2-pole dual cage clamp for 16 AWG stranded wire with ferrule or 14 AWG solid wire, 5W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/025401-10>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	LED enclosure light
<b>Series</b>	Ecoline
<b>Operating Voltage</b>	24-48 VDC
<b>Switch Type</b>	On/off
<b>Length</b>	13.8in
<b>Luminous Flux</b>	400 Lm
<b>Integral Receptacle</b>	No
<b>Mounting</b>	Magnet
<b>Connection</b>	2-pole dual cage clamp for 16 AWG stranded wire with ferrule or 14 AWG solid wire
<b>Power Consumption</b>	5W
<b>IP Rating</b>	IP20

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>