

025410-01 Cut Sheet

Stego LED enclosure light, 100-240 VAC operating voltage, motion sensor switch, 13.8in length, 400 Lm, screw mount, 2-pole plug with snap lock, 5W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/025410-01>



Technical Specifications

Brand	Stego
Item	LED enclosure light
Operating Voltage	100-240 VAC
Switch Type	Motion sensor
Length	13.8in
Luminous Flux	400 Lm
Integral Receptacle	No
Mounting	Screw
Connection	2-pole plug with snap lock
Power Consumption	5W
IP Rating	IP20
Requires	M5 mounting screws and power or extension cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/025410-01.pdf>
See store item page for other formats.