

# 025411-01 Cut Sheet

Stego LED enclosure light, 24-48 VDC operating voltage, motion sensor switch, 13.8in length, 400 Lm, screw mount, 2-pole plug with snap lock, 5W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/025411-01>



## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	LED enclosure light
<b>Operating Voltage</b>	24-48 VDC
<b>Switch Type</b>	Motion sensor
<b>Length</b>	13.8in
<b>Luminous Flux</b>	400 Lm
<b>Integral Receptacle</b>	No
<b>Mounting</b>	Screw
<b>Connection</b>	2-pole plug with snap lock
<b>Power Consumption</b>	5W
<b>IP Rating</b>	IP20
<b>Requires</b>	M5 mounting screws and power or extension cable

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/025411-01.pdf>  
See store item page for other formats.