

025421-11 Cut Sheet



Stego Ecoline LED enclosure light, 24-48 VDC operating voltage, no switch, 13.8in length, 400 Lm, screw mount, 2-pole dual cage clamp for 16 AWG stranded wire with ferrule or 14 AWG solid wire, 5W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/025421-11>

Technical Specifications

Brand	Stego
Item	LED enclosure light
Series	Ecoline
Operating Voltage	24-48 VDC
Switch Type	None
Length	13.8in
Luminous Flux	400 Lm
Integral Receptacle	No
Mounting	Screw
Connection	2-pole dual cage clamp for 16 AWG stranded wire with ferrule or 14 AWG solid wire
Power Consumption	5W
IP Rating	IP20
Requires	M5 mounting screws

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document