02550.0-01 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Stego LED enclosure light, 24–240 VAC/VDC operating voltage, on/off switch, 13.8in length, 560 lm, screw mount, 2-pole plug with snap lock, 4.5W, IP20.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/02550.0-01

Technical Specifications

Brand	Stego
Item	LED enclosure light
Operating Voltage	24–240 VAC/VDC
Switch Type	On/off
Length	13.8in
Luminous Flux	560 lm
Color Temperature	6000–7000K
Beam Angle	120 degrees
Integral Receptacle	No

Mounting	Screw
Connection	2-pole plug with snap lock
Power Consumption	4.5W
IP Rating	IP20
Rotatable	Yes
Includes	(2) mounting feet
Requires	M5 mounting screws and power or extension cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/02550.0-01.pdf
See store item page for other formats.