02552.0-10 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Stego LED enclosure light, 24–240 VAC/VDC operating voltage, no switch, 13.8in length, 560 lm, magnet mount, 2-pole pressure clamp for 16 AWG stranded wire with ferrule or 14 AWG solid wire, 4.5W, IP20.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/02552.0-10

Technical Specifications

Brand	Stego
Item	LED enclosure light
Operating Voltage	24–240 VAC/VDC
Switch Type	None
Length	13.8in
Luminous Flux	560 lm
Color Temperature	6000–7000K
Beam Angle	120 degrees

Integral Receptacle	No
Mounting	Magnet
Connection	2-pole pressure clamp for 16 AWG stranded wire with ferrule or 14 AWG solid wire
Power Consumption	4.5W
IP Rating	IP20
Rotatable	Yes
Includes	(2) mounting feet

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/02552.0-10.pdf
See store item page for other formats.