

027000-00 Cut Sheet



Stego enclosure heater, axial fan, 550W heating capacity, PTC resistor heating element, 220-240 VAC operating voltage, 50/60 Hz, adjustable thermostat, N.C. (open on rise) 0 to 60 deg C, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/027000-00>

Technical Specifications

| | |
|--------------------------|------------------|
| Brand | Stego |
| Item | Enclosure heater |
| IP Rating | IP20 |
| Fan Type | Axial |
| Heating Capacity | 550W |
| Heating Element | PTC resistor |
| Operating Voltage | 220-240 VAC |
| Hertz | 50/60 Hz |

| | |
|-------------------------------|---|
| Connection | 2-pole terminal for 14 AWG max solid or stranded wire |
| Heater Control | Adjustable thermostat |
| Contact 1 | N.C. (open on rise) 0 to 60 deg C |
| Switching Differential | 7K |
| Switching Tolerance | +/-4K |
| Mounting | 35mm DIN rail |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E204590 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/027000-00.pdf>
See store item page for other formats.