

# 027000-00 Cut Sheet



Stego enclosure heater, axial fan, 550W heating capacity, PTC resistor heating element, 220-240 VAC operating voltage, 50/60 Hz, adjustable thermostat, N.C. (open on rise) 0 to 60 deg C, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/027000-00>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Enclosure heater
<b>IP Rating</b>	IP20
<b>Fan Type</b>	Axial
<b>Heating Capacity</b>	550W
<b>Heating Element</b>	PTC resistor
<b>Operating Voltage</b>	220-240 VAC
<b>Hertz</b>	50/60 Hz
<b>Connection</b>	2-pole terminal for 14 AWG max solid or stranded wire
<b>Heater Control</b>	Adjustable thermostat
<b>Contact 1</b>	N.C. (open on rise) 0 to 60 deg C
<b>Switching Differential</b>	7K
<b>Switching Tolerance</b>	+/-4K
<b>Mounting</b>	35mm DIN rail

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E204590
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>