

027009-00 Cut Sheet



Stego enclosure heater, axial fan, 550W heating capacity, PTC resistor heating element, 100-120 VAC operating voltage, 50/60 Hz, adjustable thermostat, N.C. (open on rise) 32 to 140 deg F, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/027009-00>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP20
Fan Type	Axial
Heating Capacity	550W
Heating Element	PTC resistor
Operating Voltage	100-120 VAC
Hertz	50/60 Hz
Connection	2-pole terminal for 14 AWG max solid or stranded wire
Heater Control	Adjustable thermostat
Contact 1	N.C. (open on rise) 32 to 140 deg F
Switching Differential	13 deg F
Switching Tolerance	+/-7 deg F
Mounting	35mm DIN rail

Agency Approvals

UL Listed File #	None
UL Recognized File #	E204590
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document