

027010-00 Cut Sheet



Stego enclosure heater, axial fan, 650W heating capacity, PTC resistor heating element, 220-240 VAC operating voltage, 50/60 Hz, adjustable thermostat, N.C. (open on rise) 0 to 60 deg C, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/027010-00>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP20
Fan Type	Axial
Heating Capacity	650W
Heating Element	PTC resistor
Operating Voltage	220-240 VAC
Hertz	50/60 Hz

Connection	2-pole terminal for 14 AWG max solid or stranded wire
Heater Control	Adjustable thermostat
Contact 1	N.C. (open on rise) 0 to 60 deg C
Switching Differential	7K
Switching Tolerance	+/-4K
Mounting	35mm DIN rail

Agency Approvals

UL Listed File #	None
UL Recognized File #	E204590
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/027010-00.pdf>
See store item page for other formats.