

02802 Cut Sheet

Viking jobber-length drill bit, 3/32in, split point, high-speed steel (HSS), black oxide finish, round shank, 2.3in (58mm) overall length. Package of 10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/02802>

Technical Specifications

Brand	Viking	Point Angle	135 degrees
Item	Drill bit	Point Cut	Split
Replacement	No	Shank Type	Round
Drill Bit Type	Jobber-length	Overall Length	2.3in (58mm)
Size	3/32in	For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Material	High-speed steel (HSS)	Application	Hole cutting
Finish	Black oxide	Quantity per Pack	10
Flute Length	1-1/4in		

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement