

028100-01 Cut Sheet



Stego enclosure heater, axial fan, 400W heating capacity, touch-safe PTC resistor heating element, 230 VAC operating voltage, 50/60 Hz, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/028100-01>

Technical Specifications

| | |
|-------------------|--|
| Brand | Stego |
| Item | Enclosure heater |
| IP Rating | IP20 |
| Fan Type | Axial |
| Heating Capacity | 400W |
| Heating Element | Touch-safe PTC resistor |
| Operating Voltage | 230 VAC |
| Hertz | 50/60 Hz |
| Connection | 2-pole terminal for 14 AWG max solid or 16 AWG max stranded wire |
| Mounting | Panel |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E234324 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/028100-01.pdf>
See store item page for other formats.