

# 028109-00 Cut Sheet



Stego enclosure heater, axial fan, 400W heating capacity, touch-safe PTC resistor heating element, 120 VAC operating voltage, 50/60 Hz, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/028109-00>

## Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP20
Fan Type	Axial
Heating Capacity	400W
Heating Element	Touch-safe PTC resistor
Operating Voltage	120 VAC
Hertz	50/60 Hz
Connection	2-pole terminal for 14 AWG max solid or 16 AWG max stranded wire
Mounting	35mm DIN rail

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E150057 & E234324
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/028109-00.pdf>  
See store item page for other formats.