

# 028209-08 Cut Sheet



Stego enclosure heater, axial fan, 400W heating capacity, touch-safe PTC resistor heating element, 120 VAC operating voltage, 50/60 Hz, fixed thermostat, N.C. (open on rise) 41 deg F (5 deg C) switch-on, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/028209-08>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Enclosure heater
<b>IP Rating</b>	IP20
<b>Fan Type</b>	Axial
<b>Heating Capacity</b>	400W
<b>Heating Element</b>	Touch-safe PTC resistor
<b>Operating Voltage</b>	120 VAC
<b>Hertz</b>	50/60 Hz

<b>Connection</b>	2-pole terminal for 14 AWG max solid or 16 AWG max stranded wire
<b>Heater Control</b>	Fixed thermostat
<b>Contact 1</b>	N.C. (open on rise) 41 deg F (5 deg C) switch-on
<b>Switching Differential</b>	18 deg F (10K)
<b>Switching Tolerance</b>	+/-9 deg F (+/-5K)
<b>Mounting</b>	Panel

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E150057
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/028209-08.pdf>  
See store item page for other formats.