

028210-06 Cut Sheet



Stego enclosure heater, axial fan, 250W heating capacity, touch-safe PTC resistor heating element, 230 VAC operating voltage, 50/60 Hz, fixed thermostat, N.C. (open on rise) 41 deg F (5 deg C) switch-on, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/028210-06>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP20
Fan Type	Axial
Heating Capacity	250W
Heating Element	Touch-safe PTC resistor
Operating Voltage	230 VAC
Hertz	50/60 Hz

Connection	2-pole terminal for 14 AWG max solid or 16 AWG max stranded wire
Heater Control	Fixed thermostat
Contact 1	N.C. (open on rise) 41 deg F (5 deg C) switch-on
Switching Differential	18 deg F (10K)
Switching Tolerance	+/-9 deg F (+/-5K)
Mounting	35mm DIN rail

Agency Approvals

UL Listed File #	None
UL Recognized File #	E150057
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/028210-06.pdf>
See store item page for other formats.