

# 02962 Cut Sheet



Viking jobber-length drill bit, 11/32in, split point, high-speed steel (HSS), black oxide finish, round shank, 4.8in (122mm) overall length. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/02962>

## Technical Specifications

|                       |                        |                          |                                                       |
|-----------------------|------------------------|--------------------------|-------------------------------------------------------|
| <b>Brand</b>          | Viking                 | <b>Point Angle</b>       | 135 degrees                                           |
| <b>Item</b>           | Drill bit              | <b>Point Cut</b>         | Split                                                 |
| <b>Replacement</b>    | No                     | <b>Shank Type</b>        | Round                                                 |
| <b>Drill Bit Type</b> | Jobber-length          | <b>Overall Length</b>    | 4.8in (122mm)                                         |
| <b>Size</b>           | 11/32in                | <b>For Use On</b>        | Aluminum, brass, plastic, steel, bronze and cast iron |
| <b>Material</b>       | High-speed steel (HSS) | <b>Application</b>       | Hole cutting                                          |
| <b>Finish</b>         | Black oxide            | <b>Quantity per Pack</b> | 5                                                     |
| <b>Flute Length</b>   | 3-7/16in               |                          |                                                       |

## Agency Approvals

|                             |                                                                     |
|-----------------------------|---------------------------------------------------------------------|
| <b>UL Listed File #</b>     | N/A                                                                 |
| <b>UL Recognized File #</b> | N/A                                                                 |
| <b>UL Hazardous File #</b>  | N/A                                                                 |
| <b>CE</b>                   | None                                                                |
| <b>CSA File #</b>           | N/A                                                                 |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |