

# 03022 Cut Sheet



Viking jobber-length drill bit, 7/16in, split point, high-speed steel (HSS), black oxide finish, round shank, 5.5in (140mm) overall length. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/03022>

## Technical Specifications

<b>Brand</b>	Viking	<b>Point Angle</b>	135 degrees
<b>Item</b>	Drill bit	<b>Point Cut</b>	Split
<b>Replacement</b>	No	<b>Shank Type</b>	Round
<b>Drill Bit Type</b>	Jobber-length	<b>Overall Length</b>	5.5in (140mm)
<b>Size</b>	7/16in	<b>For Use On</b>	Aluminum, brass, plastic, steel, bronze and cast iron
<b>Material</b>	High-speed steel (HSS)	<b>Application</b>	Hole cutting
<b>Finish</b>	Black oxide	<b>Quantity per Pack</b>	5
<b>Flute Length</b>	4in		

## Agency Approvals

<b>UL Listed File #</b>	N/A
<b>UL Recognized File #</b>	N/A
<b>UL Hazardous File #</b>	N/A
<b>CE</b>	None
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>