

030820-00 Cut Sheet



Stego enclosure heater, axial fan, 700W heating capacity, high performance cartridge heating element, 230 VAC operating voltage, 50/60 Hz, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/030820-00>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP20
Fan Type	Axial
Heating Capacity	700W
Heating Element	High performance cartridge
Operating Voltage	230 VAC
Hertz	50/60 Hz
Connection	2-pole dual pressure clamp for 14 AWG max solid or 16 AWG max stranded wire
Mounting	35mm DIN rail

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/030820-00.pdf>
See store item page for other formats.