

030973-16 Cut Sheet



Stego enclosure heater, axial fan, 800W heating capacity, high performance cartridge heating element, 56 VDC operating voltage, adjustable thermostat, N.C. (open on rise) -4 to 104 deg F, foot mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/030973-16>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP20
Fan Type	Axial
Heating Capacity	800W
Heating Element	High performance cartridge
Operating Voltage	56 VDC
Heater Control	Adjustable thermostat
Contact 1	N.C. (open on rise) -4 to 104 deg F
Switching Differential	5.4 deg F
Switching Tolerance	+/-1.8 deg F
Mounting	Foot

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document