

# 032029-00 Cut Sheet



Stego enclosure heater, axial fan, 1000W heating capacity, PTC resistor heating element, 100-120 VAC operating voltage, 50/60 Hz, fixed thermostat, N.C. (open on rise) 41 deg F (5 deg C) switch-on, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/032029-00>

## Technical Specifications

|                               |  |
|-------------------------------|--|
| <b>Brand</b>                  | Stego  |
| <b>Item</b>                   | Enclosure heater                                 |
| <b>IP Rating</b>              | IP20   |
| <b>Fan Type</b>               | Axial  |
| <b>Heating Capacity</b>       | 1000W  |
| <b>Heating Element</b>        | PTC resistor                                     |
| <b>Operating Voltage</b>      | 100-120 VAC                                      |
| <b>Hertz</b>                  | 50/60 Hz   |
| <b>Connection</b>             | Male power insert connector                      |
| <b>Heater Control</b>         | Fixed thermostat                                 |
| <b>Contact 1</b>              | N.C. (open on rise) 41 deg F (5 deg C) switch-on |
| <b>Switching Differential</b> | 18 deg F (10K)                                   |
| <b>Switching Tolerance</b>    | +/-9 deg F (+/-5K)                               |
| <b>Mounting</b>               | 35mm DIN rail                                    |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E234324                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |