

04205B Cut Sheet



Hallex fitting, zinc die cast, straight, 1/2in trade size, squeeze conduit connection. Package of 25. For use with flexible metal conduit (FMC), AC cable (BX), MC cable. Screw and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/04205B>

Technical Specifications

Brand	Hallex
Item	Fitting
Liquid-tight	No
Fitting Type	Straight
Material	Zinc die cast
Trade Size	1/2in
Conduit Connection Method	Squeeze
Box Connection Type	1/2in male NPSM
Insulation	No
Knockout Size	1/2in
Reduced Wall Flexible Metal Conduit Trade Size	1/2in

Flexible Metal Conduit (FMC) Compatibility	Aluminum FMC, aluminum RWFMC, steel FMC and steel RWFMC
Armored Cable (AC) Size Range	Aluminum 6/3 and steel 6/3
Metal Clad (MC) Cable Size Range	Aluminum 6/3 and steel 6/3
Quantity per Pack	25
For Use With	Flexible metal conduit (FMC), AC cable (BX), MC cable
Includes	Screw and locknut
Applicable Standards	UL 514B Listed

Agency Approvals

UL Listed File #	E30248
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement