

04240B Cut Sheet



Halex fitting, zinc die cast, straight, 4in trade size, squeeze conduit connection. Package of 1. For use with flexible metal conduit (FMC). Screw and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/04240B>

Technical Specifications

Brand	Halex
Item	Fitting
Liquid-tight	No
Fitting Type	Straight
Material	Zinc die cast
Trade Size	4in
Conduit Connection Method	Squeeze
Box Connection Type	4in male NPSM
Insulation	No

Knockout Size	4in
Reduced Wall Flexible Metal Conduit Trade Size	4in
Flexible Metal Conduit (FMC) Compatibility	Aluminum FMC, aluminum RWFMC, steel FMC and steel RWFMC
Quantity per Pack	1
For Use With	Flexible metal conduit (FMC)
Includes	Screw and locknut
Applicable Standards	UL 514B Listed

Agency Approvals

UL Listed File #	E30248
CE	None
RoHS Status	No
EU REACH	View EU REACH document