

04412B Cut Sheet



Hallex fitting, zinc die cast, straight, 1-1/4in trade size, twist-in conduit connection. Package of 10. For use with flexible metal conduit (FMC). Locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/04412B>

Technical Specifications

| | |
|----------------------------------|-------------------|
| Brand | Hallex |
| Item | Fitting |
| Liquid-tight | No |
| Fitting Type | Straight |
| Material | Zinc die cast |
| Trade Size | 1-1/4in |
| Conduit Connection Method | Twist-in |
| Box Connection Type | 1-1/4in male NPSM |
| Insulation | No |

| | |
|---|---|
| Knockout Size | 1-1/4in |
| Reduced Wall Flexible Metal Conduit Trade Size | 1-1/4in |
| Flexible Metal Conduit (FMC) Compatibility | Aluminum FMC, aluminum RWFC, steel FMC and steel RWFC |
| Quantity per Pack | 10 |
| For Use With | Flexible metal conduit (FMC) |
| Includes | Locknut |
| Applicable Standards | UL 514B Listed |

Agency Approvals

| | |
|-------------------------|---|
| UL Listed File # | E30248 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |