

05004051055 Cut Sheet



Wera Zyklop Metal standard ratchet, driver bit, and socket set, Phillips, Pozidriv, internal hex, Torx and external hex, 29 pieces, 1in bit length, 3/8in drive, imperial.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05004051055>

Technical Specifications

Brand	Wera
Series	Zyklop Metal
Item	Ratchet, driver bit, and socket set
Number of Pieces	29
Bit Type	Standard
Measurement Type	Imperial
Insulated	No
Drive Size	3/8in
Bit Length	1in
Tip Type	Phillips, Pozidriv, internal hex, Torx and external hex
Fastening Size	1/4in, 5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in and 3/4in

Ratcheting	Yes
Directional Change	Switch lever
Return Angle	5 degrees
Lock Mechanism	Ballpoint socket
Set Includes	Ratchet, 200 mm extension with free-turning sleeve, 76 mm wobble extension, 3/8 inch x 1/4 inch x 44 mm long bit adapter, (9) sockets (1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16 and 3/4 inch), (3) Phillips bits (#1, #2 and #3), (2) Pozidriv bits (#1 and #2), (5) Hex-Plus bits (5/32, 3/16, 7/32, 1/4 and 5/16 inch), (6) Torx bits (T15, T20, T25, T27, T30 and T40), durable cloth pouch
Application	Ratcheting, screwdriving and bit holding

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document