

05004078055 Cut Sheet



Wera Zyklop Metal standard ratchet, driver bit, and socket set, Phillips, internal hex, Torx and external hex, 28 pieces, 1in bit length, 1/2in drive, metric.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05004078055>

Technical Specifications

Brand	Wera
Series	Zyklop Metal
Item	Ratchet, driver bit, and socket set
Number of Pieces	28
Bit Type	Standard
Measurement Type	Metric
Insulated	No
Drive Size	1/2in
Bit Length	1in
Tip Type	Phillips, internal hex, Torx and external hex
Fastening Size	10mm, 11mm, 12mm, 13mm, 14mm, 15mm, 16mm, 17mm, 18mm and 19mm

Ratcheting	Yes
Directional Change	Switch lever
Return Angle	5 degrees
Lock Mechanism	Ballpoint socket
Set Includes	Ratchet, 250mm extension with free-turning sleeve, 52mm wobble extension, 1/2in x 5/16in x 50mm long bit adapter, (10) sockets (10, 11, 12, 13, 14, 15, 16, 17, 18 and 19mm), (2) Phillips bits (#2 and #3), (4) Hex-Plus bits (5, 6, 8 and 10mm), (8) Torx bits (T20, T25, T27, T30, T40, T45, T50 and T55), durable cloth pouch
Application	Ratcheting, screwdriving and bit holding

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document