

05004081055 Cut Sheet



Wera Zyklop Metal standard ratchet, driver bit, and socket set, Phillips, internal hex, Torx and external hex, 28 pieces, 1in bit length, 1/2in drive, imperial.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05004081055>

Technical Specifications

Brand	Wera
Series	Zyklop Metal
Item	Ratchet, driver bit, and socket set
Number of Pieces	28
Bit Type	Standard
Measurement Type	Imperial
Insulated	No
Drive Size	1/2in
Bit Length	1in
Tip Type	Phillips, internal hex, Torx and external hex
Fastening Size	3/8in, 7/16in, 1/2in, 9/16in, 19/32in, 5/8in, 11/16in, 3/4in, 25/32in and 13/16in

Ratcheting	Yes
Directional Change	Switch lever
Return Angle	5 degrees
Lock Mechanism	Ballpoint socket
Set Includes	Ratchet, 250mm extension with free-turning sleeve, 52mm wobble extension, 1/2in x 5/16in x 50mm long bit adapter, (10) sockets (3/8, 7/16, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 25/32 and 13/16in), (2) Phillips bits (#2 and #3), (4) Hex-Plus bits (7/32, 1/4, 5/16 and 3/8in), (8) Torx bits (T20, T25, T27, T30, T40, T45, T50 and T55), durable cloth pouch
Application	Ratcheting, screwdriving and bit holding

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document