

# 05004081055 Cut Sheet



Wera Zyklop Metal standard ratchet, driver bit, and socket set, 28 pieces, 1in bit length, 1/2in drive, imperial.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05004081055>

## Technical Specifications

<b>Brand</b>	Wera
<b>Series</b>	Zyklop Metal
<b>Item</b>	Ratchet, driver bit, and socket set
<b>Number of Pieces</b>	28
<b>Bit Type</b>	Standard
<b>Measurement Type</b>	Imperial
<b>Insulated</b>	No
<b>Drive Size</b>	1/2in
<b>Bit Length</b>	1in
<b>Tip Type</b>	Phillips, hex and Torx
<b>Fastening Size</b>	3/8in, 7/16in, 1/2in, 9/16in, 19/32in, 5/8in, 11/16in, 3/4in, 25/32in and 13/16in
<b>Ratcheting</b>	Yes
<b>Directional Change</b>	Switch lever
<b>Return Angle</b>	5 degrees
<b>Lock Mechanism</b>	Secure socket ball lock mechanism
<b>Set Includes</b>	Ratchet, 250mm extension with free-turning sleeve, 52mm wobble extension, 1/2in x 5/16in x 50mm long bit adapter, (10) sockets (3/8, 7/16, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 25/32 and 13/16in), (2) Phillips bits (#2 and #3), (4) Hex-Plus bits (7/32, 1/4, 5/16 and 3/8in), (8) Torx bits (T20, T25, T27, T30, T40, T45, T50 and T55), durable cloth pouch
<b>Application</b>	Ratcheting, screwdriving and bit holding

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>