

05006611001 Cut Sheet



Wera Kraftform Kompakt VDE insulated multi-bit screwdriver, 1000V insulation rating, 17 pieces, Kraftform ergonomic handle, 4.0in (102mm) shaft length, Phillips, Pozidriv, Pozidriv/slotted, Torx and slotted.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05006611001>

Technical Specifications

Brand	Wera
Series	Kraftform Kompakt VDE
Item	Screwdriver
Screwdriver Type	Insulated multi-bit
Number of Pieces	17
Ratcheting	No
Insulated	Yes
Insulation Rating	1000V
Lock Mechanism	Ring release
Shaft Length	4.0in (102mm)
Shaft Diameter	0.28in (7.0mm)
Handle Length	3.9in (99mm)

Handle Type	Kraftform ergonomic handle
Tip Type	Phillips, Pozidriv, Pozidriv/slotted, Torx and slotted
Includes	(2) Kraftform VDE handles for interchangeable blades, (15) VDE blade shafts (slotted: (2.5mm, 3.5mm, 4mm, 5.5mm, 6.5mm), Phillips: (#1, #2), Pozidriv: (#1, #2), Pozidriv/slotted: (#1, #2), Torx: (T10, T15, T20, T25), (1) robust folding pouch
Application	Screwdriving
Applicable Standards	IEC 60900
Package Type	Robust folding pouch

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	False
RoHS Status	No
EU REACH	View EU REACH document