

05006619001 Cut Sheet



Wera Kraftform Kompakt VDE insulated multi-bit screwdriver, 1000V insulation rating, 17 pieces, ratcheting, imperial, Kraftform ergonomic handle, 4.0in (102mm) shaft length, Phillips, Pozidriv/slotted, Torx, slotted and square.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05006619001>

Technical Specifications

| | |
|--------------------------|-----------------------|
| Brand | Wera |
| Series | Kraftform Kompakt VDE |
| Item | Screwdriver |
| Screwdriver Type | Insulated multi-bit |
| Number of Pieces | 17 |
| Ratcheting | Yes |
| Insulated | Yes |
| Insulation Rating | 1000V |
| Lock Mechanism | Ring release |
| Measurement Type | Imperial |
| Shaft Length | 4.0in (102mm) |
| Shaft Diameter | 0.28in (7.0mm) |

| | |
|-----------------------------|--|
| Handle Type | Kraftform ergonomic handle |
| Tip Type | Phillips, Pozidriv/slotted, Torx, slotted and square |
| Includes | (1) Kraftform VDE handle for interchangeable blades, (1) Kraftform ratcheting VDE handle for interchangeable blades, (15) VDE blade shafts (Phillips: (#1, #2), Pozidriv/slotted: (#1, #2), Torx: (T10, T15, T20, T25), slotted: (2.5mm, 3.5mm, 4mm, 5.5mm, 6.5mm), square: (#1, #2), (1) robust folding pouch |
| Application | Screwdriving |
| Applicable Standards | IEC 60900 |
| Package Type | Robust folding pouch |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | False |
| RoHS Status | No |
| EU REACH | View EU REACH document |