



Wera Kraftform Kompakt VDE Turbo insulated multi-bit screwdriver, 1000V insulation rating, 16 pieces, Kraftform ergonomic handle, 4.0in (102mm) shaft length, Phillips, Pozidriv/slot, Pozidriv, Torx and slotted.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05006640001>

## Technical Specifications

<b>Brand</b>	Wera
<b>Series</b>	Kraftform Kompakt VDE Turbo
<b>Item</b>	Screwdriver
<b>Screwdriver Type</b>	Insulated multi-bit
<b>Number of Pieces</b>	16
<b>Ratcheting</b>	No
<b>Insulated</b>	Yes
<b>Insulation Rating</b>	1000V
<b>Lock Mechanism</b>	Ring release
<b>Shaft Length</b>	4.0in (102mm)
<b>Shaft Diameter</b>	0.28in (7.0mm)
<b>Handle Length</b>	3.9in (99mm)
<b>Handle Type</b>	Kraftform ergonomic handle

<b>Tip Type</b>	Phillips, Pozidriv/slot, Pozidriv, Torx and slotted
<b>Includes</b>	(1) Kraftform VDE handle for interchangeable VDE blades, (1) Kraftform Turbo VDE handle for interchangeable VDE blades, (14) reduced shank VDE blade shafts (Phillips: (#1, #2), Pozidriv/slot: (#1, #2), Pozidriv: (#1, #2), slotted: (2.5, 3.5, 4, 5.5mm), Torx: (T10, T15, T20, T25), (1) durable cloth pouch
<b>Application</b>	Screwdriving
<b>Applicable Standards</b>	IEC 60900
<b>Tool Features</b>	4x screwdriving speed with turbo function
<b>Package Type</b>	Durable cloth pouch

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	False
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>