

05006641001 Cut Sheet



Wera Kraftform Kompakt VDE Turbo insulated multi-bit screwdriver, 1000V insulation rating, 16 pieces, imperial, Kraftform ergonomic handle, 4.0in (102mm) shaft length, Phillips, PlusMinus, Torx, slotted and square.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05006641001>

Technical Specifications

Brand	Wera
Series	Kraftform Kompakt VDE Turbo
Item	Screwdriver
Screwdriver Type	Insulated multi-bit
Number of Pieces	16
Ratcheting	No
Insulated	Yes
Insulation Rating	1000V
Lock Mechanism	Ring release
Measurement Type	Imperial
Shaft Length	4.0in (102mm)
Shaft Diameter	0.28in (7.0mm)
Handle Length	3.9in (99mm)

Handle Type	Kraftform ergonomic handle
Tip Type	Phillips, PlusMinus, Torx, slotted and square
Includes	(1) Kraftform VDE handle for interchangeable VDE blades, (1) Kraftform Turbo VDE handle for interchangeable VDE blades, (14) reduced shank VDE blade shafts (Phillips: (#1, #2), Plus/Minus: #1, #2), slotted: (2.5, 3.5, 4, 5.5mm), Torx: (T10, T15, T20, T25), square: (#1, #2)), (1) durable cloth pouch
Application	Screwdriving
Applicable Standards	IEC 60900
Tool Features	4x screwdriving speed with turbo function
Package Type	Durable cloth pouch

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	False
RoHS Status	No
EU REACH	View EU REACH document