



Wera Tool-Check PLUS standard socket and driver bit set, ratcheting, Phillips, Pozidriv, Torx, tamperproof torx, internal hex, external hex, slotted and square, 39 pieces, 1in bit length, 1/4in drive, metric, compact Tool-Check storage system.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05049055001>

Technical Specifications

Brand	Wera	Return Angle	6 degrees
Series	Tool-Check PLUS	Lock Mechanism	Ballpoint socket, retaining ring bit holder and Rapidaptor quick-release bit holder
Item	Socket and driver bit set	Set Includes	Includes (1) 1/4in Zykllop mini bit ratchet, (1) 1/4in bit holding screwdriver, (1) 1/4in Rapidaptor universal bit holder, (1) 1/4in hex to square adapter, (7) Zykllop 1/4in sockets (5.5mm, 6mm, 7mm, 8mm, 10mm, 12mm, 13mm), (28) 1in standard driver bits (Phillips: (2) #1, (3) #2, #3, slotted: 5.5mm, torx: (T10, T15, T20, T25, T30, T40), tamperproof torx: (T10, T15, T20, T25, T30), hex: (3mm, 4mm, 5mm, 6mm, 8mm), Pozidriv: (#1, (3) #2, #3), (1) Bit-Check storage system
Number of Pieces	39	Application	Bit holding, screwdriving and fastening
Bit Type	Standard	Package Type	Compact Tool-Check storage system
Measurement Type	Metric		
Insulated	No		
Drive Size	1/4in		
Bit Length	1in		
Tip Type	Phillips, Pozidriv, Torx, tamperproof torx, internal hex, external hex, slotted and square		
Ratcheting	Yes		
Directional Change	Switch lever		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	False
RoHS Status	No
EU REACH	View EU REACH document