

05051045055 Cut Sheet



Wera Zyklop Speed standard ratchet, driver bit, and socket set, Phillips, Pozidriv, Torx, hex and slotted, 26 pieces, 2in bit length, 1/4in drive, metric.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05051045055>

Technical Specifications

Brand	Wera
Series	Zyklop Speed
Item	Ratchet, driver bit, and socket set
Number of Pieces	26
Bit Type	Standard
Measurement Type	Metric
Insulated	No
Drive Size	1/4in
Bit Length	2in
Tip Type	Phillips, Pozidriv, Torx, hex and slotted
Fastening Size	5.5mm, 6mm, 7mm, 8mm, 10mm, 11mm, 12mm and 13mm

Ratcheting	Yes
Directional Change	Switch lever
Return Angle	5 degrees
Lock Mechanism	Ballpoint socket
Set Includes	Ratchet, 150 mm extension with free-turning sleeve, 1/4 inch x 1/4 inch x 37 mm long bit adapter, (7) 1/4 inch drive sockets (5.5, 6, 7, 8, 10, 12 and 13 mm), 5.5 mm flat/slotted bit, (3) Phillips bits (#1, #2 and #3), (2) Pozidriv bits (#1 and #2), (4) Hex-Plus bits (3, 4, 5 and 6 mm), (6) Torx bits (T10, T15, T20, T25, T27 and T30), durable cloth pouch
Application	Ratcheting, screwdriving and bit holding

Agency Approvals

RoHS Status	No
EU REACH	View EU REACH document