

05051530001 Cut Sheet



Wera Kraftform Kompakt multi-bit screwdriver, 17 pieces, ratcheting, metric, Kraftform ergonomic handle, 3.5in (89mm) shaft length, Phillips, Pozidriv, tamperproof torx, external hex and slotted.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05051530001>

Technical Specifications

Brand	Wera
Series	Kraftform Kompakt
Item	Screwdriver
Screwdriver Type	Multi-bit
Number of Pieces	17
Ratcheting	Yes
Insulated	No
Lock Mechanism	Rapidaptor quick-release bit holder
Measurement Type	Metric
Shaft Length	3.5in (89mm)
Handle Length	4.3in (109mm)

Handle Type	Kraftform ergonomic handle
Tip Type	Phillips, Pozidriv, tamperproof torx, external hex and slotted
Includes	(1) Kraftform Kompakt Rapidaptor bit holding ratcheting screwdriver, (16) 3.5in standard bits (Phillips: #1, #2, #3 Pozidriv: #1, #2, #3, tamperproof torx: T10, T15, T20, T25, T30, external hex: 3mm, 4mm, 5mm, 6mm, slotted: 5.5mm), (1) robust textile pouch
Application	Bit holding and screwdriving
Package Type	Robust folding pouch

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	False
RoHS Status	No
EU REACH	View EU REACH document