

05056490001 Cut Sheet



Wera Tool-Check PLUS standard socket and driver bit set, Phillips, slotted, Torx, tamperproof torx, internal hex, external hex and Pozidriv, 39 pieces, 1in bit length, 1/4in drive, metric.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05056490001>

Technical Specifications

Brand	Wera
Series	Tool-Check PLUS
Item	Socket and driver bit set
Number of Pieces	39
Bit Type	Standard
Measurement Type	Metric
Insulated	No
Drive Size	1/4in
Bit Length	1in
Tip Type	Phillips, slotted, Torx, tamperproof torx, internal hex, external hex and Pozidriv
Ratcheting	Yes
Directional Change	Dial switch

Return Angle	6 degrees
Lock Mechanism	Ballpoint socket, retaining ring bit holder and Rapidaptor quick-release bit holder
Set Includes	(1) 1/4in Zyklop mini bit ratchet, (1) 1/4in bitholding screwdriver, (1) 1/4in Rapidaptor universal bit holder, (1) 1/4in hex to square adaptor, (7) Zyklop 1/4in sockets (5.5mm, 6mm, 7mm, 8mm, 10mm, 12mm, 13mm), (28) 1in standard driver bits (Phillips: (2) #1, (3) #2, #3, slotted: 5.5mm, torx: (T10, T15, T20, T25, T30, T40), tamperproof torx: (T10, T15, T20, T25, T30), hex: (3mm, 4mm, 5mm, 6mm, 8mm), Pozidriv: (#1, (3) #2, #3), (1) Bit-Check storage system
Application	Bit holding, screwdriving and ratcheting

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document