

05056491001 Cut Sheet



Wera Tool-Check standard socket and driver bit set, Phillips, slotted, Torx, tamperproof torx, internal hex, square and external hex, 39 pieces, 1in bit length, 1/4in drive, imperial.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05056491001>

Technical Specifications

Brand	Wera
Series	Tool-Check
Item	Socket and driver bit set
Number of Pieces	39
Bit Type	Standard
Measurement Type	Imperial
Insulated	No
Drive Size	1/4in
Bit Length	1in
Tip Type	Phillips, slotted, Torx, tamperproof torx, internal hex, square and external hex
Fastening Size	3/16in, 1/4in, 5/16in, 11/32in, 3/8in, 7/16in and 1/2in
Ratcheting	Yes

Directional Change	Dial switch
Return Angle	4.5 degrees
Lock Mechanism	Ballpoint socket, retaining ring bit holder and Rapidaptor quick-release bit holder
Set Includes	(1) 1/4in bit ratchet, (1) bitholding screwdriver, (1) Rapidaptor universal bit holder, (1) 1/4in hex to square adaptor, (7) Zyklop 1/4in sockets (3/16in, 1/4in, 5/16in, 11/32in, 3/8in, 7/16in, 1/2in), (28) 1in standard driver bits (Phillips: (2) #1, (3) #2, (1) #3, slotted: 5.5mm, torx: (T10, T15, T20, T25, T30, T40), tamperproof torx: (T10, T15, T20, T25, T30), hex: (3/32in, 1/8in, 5/32in 3/16in, 1/4in), square: (#1, (3) #2, #3), (1) Bit-Check storage system
Application	Bit holding, screwdriving and ratcheting

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	No
EU REACH	View EU REACH document