

# 05073220055 Cut Sheet



Wera Tool-Check standard driver bit and socket set, Phillips, Pozidriv, slotted, Torx, tamperproof torx, internal hex and external hex, 38 pieces, 1in bit length, 1/4in drive, metric.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05073220055>

## Technical Specifications

Brand	Wera
Series	Tool-Check
Item	Driver bit and socket set
Number of Pieces	38
Bit Type	Standard
Measurement Type	Metric
Insulated	No
Drive Size	1/4in
Bit Length	1in
Tip Type	Phillips, Pozidriv, slotted, Torx, tamperproof torx, internal hex and external hex
Fastening Size	5.5mm, 6mm, 7mm, 8mm, 10mm, 12mm and 13mm

Ratcheting	Yes
Directional Change	Switch lever
Return Angle	6 degrees
Lock Mechanism	Ballpoint socket, retaining ring bit holder and Rapidaptor quick-release bit holder
Set Includes	Ratchet, 1/4in Rapidaptor universal bit holder, 1/4in socket drive adapter, (7) sockets (5.5, 6, 7, 8, 10, 12 and 13mm), 5.5mm slotted bit, (6) Phillips bits (#3, (2) #1, (3) #2), (5) Pozidriv bits (#1, #3, (3) #2), (5) Hex-Plus bits (3, 4, 5, 6, 8mm), (6) Torx bits (T10, T15, T20, T25, T30, T40), (5) Tamper-proof Torx bits (T10, T15, T20, T25, T30), plastic case
Application	Bit holding, screwdriving and ratcheting

## Agency Approvals

RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>