05073220055 Cut Sheet

Wera Tool-Check driver bit and socket set, ratcheting, Phillips, Pozidriv, slotted, Torx, tamperproof torx, internal hex and external hex, 38 pieces, 1in bit length, 1/4in drive, metric.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/05073220055

Technical Specifications

Brand	Wera
Series	Tool-Check
Item	Driver bit and socket set
Number of Pieces	38
Bit Type	Standard
Impact Rated	No
Measurement Type	Metric
Insulated	No
Drive Size	1/4in
Bit Length	1in
Tip Type	Phillips, Pozidriv, slotted, Torx, tamperproof torx, internal hex and external hex
Ratcheting	Yes

Directional Change	Switch lever
Return Angle	6 degrees
Lock Mechanism	Ballpoint socket, retaining ring bit holder and Rapidaptor quick-release bit holder
Set Includes	Includes ratchet, 1/4in Rapidaptor universal bit holder, 1/4in socket drive adapter, (7) sockets (5.5, 6, 7, 8, 10, 12 and 13mm), 5.5mm slotted bit, (6) Phillips bits (#3, (2) #1, (3) #2), (5) Pozidriv bits (#1, #3, (3) #2), (5) Hex-Plus bits (3, 4, 5, 6, 8mm), (6) Torx bits (T10, T15, T20, T25, T30, T40), (5) Tamper-proof Torx bits (T10, T15, T20, T25, T30), plastic case
Application	Bit holding, screwdriving and ratcheting

Agency Approvals

RoHS Status	No
EU REACH	View EU REACH document