



Wera Zyklop Speed standard ratchet, driver bit and socket set, Torx, external hex and internal hex, 37 pieces, steel, 1in and 4in bit length, 1/4in drive, imperial and metric, ballpoint holding function, foam tray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05150110001>

Technical Specifications

| | |
|---------------------------|-------------------------------------|
| Brand | Wera |
| Series | Zyklop Speed |
| Item | Ratchet, driver bit and socket set |
| Number of Pieces | 37 |
| Bit Type | Standard |
| Measurement Type | Imperial and metric |
| Material | Steel |
| Insulated | No |
| Drive Size | 1/4in |
| Bit Length | 1in and 4in |
| Tip Type | Torx, external hex and internal hex |
| Ratcheting | Yes |
| Directional Change | Dial switch |
| Return Angle | 5 degrees |

| | |
|-----------------------|--|
| Lock Mechanism | Ballpoint socket |
| Set Includes | Includes (1) 1/4in Zyklop Speed ratchet, (2) 1/4in extension with free-turning sleeve (75mm, 150mm), (1) 1/4in Zyklop universal joint, (1) 1/4in 56mm wobble extension, (14) 1/4in x 1in standard sockets (4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15mm), (5) 1/4in x 1in external hex socket bits with holding function (3, 4, 5, 6, 8mm), (4) 1/4in x 4in external hex socket bits with holding function (4, 5, 6, 8mm), (9) 1/4 x 1in Torx socket bits with holding function (T8, T9, T10, T15, T20, T25, T27, T30, T40), (1) foam tray |
| Application | Ratcheting and tray storage |
| Package Type | Foam tray |
| Tray Size | 1/4 drawer (15.4 x 6.8 x 1.4in) |
| Tool Features | Ballpoint holding function |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | False |
| RoHS Status | No |
| EU REACH | View EU REACH document |