

05347108055 Cut Sheet



Wera Kraftform Kompakt insulated multi-bit screwdriver, 1000V insulation rating, 18 pieces, Kraftform ergonomic handle, 4.0in (102mm) shaft length, Phillips, Pozidriv, PlusMinus, slotted and square.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/05347108055>

Technical Specifications

Brand	Wera
Series	Kraftform Kompakt
Item	Screwdriver
Screwdriver Type	Insulated multi-bit
Number of Pieces	18
Insulated	Yes
Insulation Rating	1000V
Shaft Length	4.0in (102mm)
Shaft Diameter	0.28in (7.0mm)
Handle Length	3.9in (98mm)
Handle Type	Kraftform ergonomic handle
Tip Type	Phillips, Pozidriv, PlusMinus, slotted and square
Includes	(2) Kraftform handles for interchangeable VDE blades, (4) VDE slotted blades (2.5, 3.5, 4, 5.5mm), (2) VDE Phillips blades (#1, #2), (2) VDE Phillips/slotted blades (#1, #2), (2) VDE Pozidriv/slotted blades (#1, #2), (2) VDE square socket blades (#1, #2), (2) square enclosure latch key blades (6, 8mm), (1) triangle enclosure latch key blade (9mm), (1) double-bit enclosure latch key blade, durable cloth pouch
Application	Screwdriving and control cabinet access
Applicable Standards	IEC 60900

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	None