

060000-00 Cut Sheet



Stego enclosure heater, 50W heating capacity, touch-safe PTC resistor heating element, 120-240 VAC/VDC operating voltage, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/060000-00>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP20
Heating Capacity	50W
Heating Element	Touch-safe PTC resistor
Operating Voltage	120-240 VAC/VDC
Connection	4-pole terminal for 14 AWG max solid or stranded wire
Mounting	35mm DIN rail

Agency Approvals

UL Listed File #	None
UL Recognized File #	E150057
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/060000-00.pdf>
See store item page for other formats.