

060110-00 Cut Sheet



Stego enclosure heater, 100W heating capacity, touch-safe PTC resistor heating element, 120-240 VAC operating voltage, fixed thermostat, N.C. (open on rise) 41 deg F (5 deg C) switch-on, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/060110-00>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP20
Heating Capacity	100W
Heating Element	Touch-safe PTC resistor
Operating Voltage	120-240 VAC
Connection	4-pole terminal for 14 AWG max solid or stranded wire
Heater Control	Fixed thermostat
Contact 1	N.C. (open on rise) 41 deg F (5 deg C) switch-on
Switching Differential	18 deg F (10K)
Switching Tolerance	+/-9 deg F (+/-5K)
Mounting	35mm DIN rail

Agency Approvals

UL Listed File #	None
UL Recognized File #	E150057
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/060110-00.pdf>
See store item page for other formats.