

# 06072 Cut Sheet



Viking jobber-length drill bit set, 13 pieces, high-speed steel (HSS), round shank, imperial, black oxide finish, metal index case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/06072>

## Technical Specifications

<b>Brand</b>	Viking	<b>Point Cut</b>	Split
<b>Item</b>	Drill bit set	<b>Shank Type</b>	Round
<b>Number of Pieces</b>	13	<b>Application</b>	Hole cutting
<b>Material</b>	High-speed steel (HSS)	<b>For Use On</b>	Stainless steel, iron and steel
<b>Drill Bit Type</b>	Jobber-length	<b>Measurement Type</b>	Imperial
<b>Drill Bit Size</b>	1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 11/64in, 3/16in, 13/64in, 7/32in, 15/64in and 1/4in	<b>Package Type</b>	Metal index case
<b>Finish</b>	Black oxide	<b>Set Includes</b>	Includes (13) jobber-length drill bits (1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 11/64in, 3/16in, 13/64in, 7/32in, 15/64in, 1/4in), durable metal case
<b>Point Angle</b>	135 degrees		

## Agency Approvals

<b>UL Listed File #</b>	N/A
<b>UL Recognized File #</b>	N/A
<b>UL Hazardous File #</b>	N/A
<b>CE</b>	None
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>