

061009-00 Cut Sheet



Stego flat heater, 50W heating capacity, resistance heating element, 120 VAC operating voltage, 50/60 Hz, M6 screw mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/061009-00>

Technical Specifications

Brand	Stego
Item	Flat heater
IP Rating	IP20
Heating Capacity	50W
Heating Element	Resistance
Operating Voltage	120 VAC
Hertz	50/60 Hz
Connection	3.3ft silicone cable with (3) 18 AWG conductors
Mounting	M6 screw
Requires	M6 mounting screws

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/061009-00.pdf>
See store item page for other formats.