

# 061009-00 Cut Sheet



Stego flat heater, 50W heating capacity, PTC resistor heating element, 120 VAC operating voltage, 50/60 Hz, M6 screw mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/061009-00>

---

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Flat heater
<b>IP Rating</b>	IP20
<b>Heating Capacity</b>	50W
<b>Heating Element</b>	PTC resistor
<b>Operating Voltage</b>	120 VAC
<b>Hertz</b>	50/60 Hz
<b>Connection</b>	3.3ft silicone cable with (3) 18 AWG conductors
<b>Mounting</b>	M6 screw

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>