

06102 Cut Sheet



Viking jobber-length drill bit set, 29 pieces, high-speed steel (HSS), round shank, imperial, black oxide finish, metal index case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/06102>

Technical Specifications

Brand	Viking
Item	Drill bit set
Number of Pieces	29
Material	High-speed steel (HSS)
Drill Bit Type	Jobber-length
Drill Bit Size	1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 11/64in, 3/16in, 13/64in, 7/32in, 15/64in, 1/4in, 17/64in, 9/32in, 19/64in, 5/16in, 21/64in, 11/32in, 23/64in, 3/8in, 25/64in, 13/32in, 27/64in, 7/16in, 29/64in, 15/32in, 31/64in and 1/2in
Finish	Black oxide
Point Angle	135 degrees

Point Cut	Split
Shank Type	Round
Application	Hole cutting
For Use On	Stainless steel, iron and steel
Measurement Type	Imperial
Package Type	Metal index case
Set Includes	Includes (29) jobber-length drill bits (1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 11/64in, 3/16in, 13/64in, 7/32in, 15/64in, 1/4in, 17/64in, 9/32in, 19/64in, 5/16in, 21/64in, 11/32in, 23/64in, 3/8in, 25/64in, 13/32in, 27/64in, 7/16in, 29/64in, 15/32in, 31/64in, 1/2in), durable metal case

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement