

06260 Cut Sheet



Viking screw-machine-length drill bit, 5/16in, split point, high-speed steel (HSS), black oxide finish, round shank, 2.8in (71mm) overall length. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/06260>

Technical Specifications

Brand	Viking	Point Angle	135 degrees
Item	Drill bit	Point Cut	Split
Replacement	No	Shank Type	Round
Drill Bit Type	Screw-machine-length	Overall Length	2.8in (71mm)
Size	5/16in	For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Material	High-speed steel (HSS)	Application	Hole cutting
Finish	Black oxide	Quantity per Pack	5
Flute Length	1-5/8in		

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement