

# 06503.0-00 Cut Sheet



Stego enclosure heater, 100W heating capacity, touch-safe PTC resistor heating element, 120-240 VAC/VDC operating voltage, 50/60 Hz, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/06503.0-00>

## Technical Specifications

|                          |   |
|--------------------------|---|
| <b>Brand</b>             | Stego   |
| <b>Item</b>              | Enclosure heater  |
| <b>IP Rating</b>         | IP20  |
| <b>Heating Capacity</b>  | 100W  |
| <b>Heating Element</b>   | Touch-safe PTC resistor   |
| <b>Operating Voltage</b> | 120-240 VAC/VDC   |
| <b>Hertz</b>             | 50/60 Hz  |
| <b>Connection</b>        | Pressure clamps for (2) 14 AWG max stranded (with wire ferrule) or solid wire |
| <b>Mounting</b>          | 35mm DIN rail or panel  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E234324                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |